
# Pro-Line II Filing Frame





# Efficiency in the office.

The Pro-Line II Filing Frame is the perfect solution in regards to the professional equipment of office cabinets. It combines innovative technology with highly functional design. Its comfort features offer tangible advantages regarding its usage. The results are low production costs combined with high customer satisfaction.

Standard colour: black Other colours available on request



- Schock full extension slide Load capacity 70 Kg (dynamic)
- **50 mm over-extension**Easy access and tabbing of filing maps
- **70 mm self-closing device** Safe closing function
- Rack + pinion parallel guidance One single locking device is sufficient
- Modular filing frame
  Final assembly without tools
  Same assemblies for all cabinets
  Premounting of filing frame possible
- Frame detachable from the slides
  Easy disassembly and reassembly
- Locking systems
  adaptable to modern locking systems
  from Huwil, Lehmann, Ojmar ...

# Triple customer benefit.

#### Easy access

The 50 mm over-extension allows for a perfect access to the rear storage space. Protrusions or handles have no negative effect on the convenience of handling. The filing maps can be comfortably removed and filed.



#### 2. Safe closing


The 70 mm self closing device guarantees a safe and complete closing of the frame. Malfunctions and damages of the furniture are being avoided. A damping feature is available on request.

#### 3. Perfect motion

The rack + pinion parallel guidance ensures a synchronized movement. For instance, it allows closing the drawer from the corner without the jamming or racking of the filing frame.




# Schock ball bearing slide with rack + pinion parallel guidance.



High load capacity Load rate 70 Kg LGA-tested with 100.000 cycles

# Maintenance-free Dirt will be automatically displaced by the balls

Long life durability Lateral impacts will be absorbed elastically




# Final assembly without tools.

The cabinet brackets are screwed into the side walls before the final cabinet assembly. At the end of the production, the filing frame will be mounted without tools. This modular system provides a high flexibility in production as well as considerably low storage costs.



#### Assembly:








- (1) Screw-in the cabinet brackets Hole patterns see page 6-9
- (2) Attach the slide modules Front cutout of cabinet brackets for installation with front cover. Rear cutout for installation behind doors (see page 8-9)
- (3) Attach the front and rear panel
- (4) Insert the connection rod

Push both pinion retainer clips (left and right) towards the pinion wheels until they click into place

Order data for basic equipment see page 18-19 Order data for accessories see page 13



#### Disassembly:







- (1) Pull out the filing frame
- (2) Detach the pinion retainer clips
  Lift latch and pull the clip backwards
- (3) Remove the connection rod
- (4) Remove the filing frame (see illustration)

Lock rear panel by bending over the latch at the slide panel. Lift frame at the frontside and pull forward until the bayonet lancings are released, then take off the frame.


# Vertical graduation system 25 mm.






<sup>\*</sup> Regarding cabinets with a front cover, the hole pattern in the side walls has to be adjusted accordingly in case of additional tacks being used to stop the front cover 1-2 mm before the front edge of the cabinet.


# Vertical graduation system 32 mm.






\* Regarding cabinets with a front cover, the hole pattern in the side walls has to be adjusted accordingly in case of additional tacks being used to stop the front cover 1-2 mm before the front edge of the cabinet.

# Depth dimensions for cabinets with front cover.




# Depth dimensions for cabinets with doors or shutters.



## Width variations.

Standard Pro-Line II filing frames are configured for single cabinets with 19 mm side walls. However, by inserting spacers they can also be used with row cabinets or even adapted to side walls with 16 mm thickness. This allows the same frame to be used for all cabinet variations.

The spacers are mounted between the cabinet bracket and the cabinet wall. When a locking system is present, the locking rod is routed between the spacer and the cabinet bracket.






<b>Cabinet type</b>		Spacer type	Demand	Article No.	UQ
Row cabinet	19 mm	Spacer 9,5 mm	2 pieces	092.06667H	20 pcs.
Single cabinet	16 mm	Spacer 3,0 mm	each	092.06666Н	20 pcs.
Row cabinet	16 mm	Spacer 11,0 mm	side wall	092.06668H	20 pcs.

# Locking systems.

An adaptation to a locking system can be achieved by using the respective lock-catch plates which will be mounted on the sides of the filing frame. In the shrouds there are holes for installation with a front cover or behind doors (offset 22 mm). The locking bar will be mounted between the cabinet bracket and the side wall.

Because of its involute toothing and the double cog rows, the rack + pinion parallel guidance meets the provided blocking forces for locking systems. Therefore, a single locking device is sufficient.





Description	Side	Colour	Article No.	UQ
Lock-catch plate Huwil SVS3	right *	silver grey	092.06674Z	20 pcs.
Lock-catch plate Lehmann Simultan Stop	right *	silver grey	092.06675Z	20 pcs.
Lock-catch plate Ojmar Sistema 1038	right *	silver grey	092.06676Z	20 pcs.
Lock-catch plate Standard	right *	silver grey	092.06677H	10 pcs.

<sup>\*</sup> Lock-catch plates for the left-hand side available on request

# Width variations - Special solutions.

Standard Pro-Line II filing frames have shrouds for completely concealing the slides.


The variant with half shrouds offers a space savings of 6 mm per side, e.g. for installation behind doors (2).


The variant with mixed shrouds allows it to achieve the required partition also with reduced interior width, e.g. 3 x A4 in cabinets with horizontal shutters (3).

Variant (4) is an alternative when locking mechanisms are not needed.



Further specialities, e.g. filing frames with integrated blocking device "Tilt-Control" please find in our brochure "Filing frame Basic-Line".





Cabinet width / Frame partition	Frame width	Inte	rior cal	binet w	idth
	[mm]	(1)	(2)	(3)	(4)
Overall cabinet width 600 mm*	480	562	562		~~
Overall cabinet width 800 mm*	680	762	762		
Overall cabinet width 1000 mm*	880	962	962		
Overall cabinet width 1200 mm*	1080	1162	1162		
Partition 1 x A4	324	406	406	396	385
Partition 2 x A4 or 3 x A5	676	758	758	748	737
Partition 3 x A4	1028	1110	1110	1100	1089

<sup>\*</sup> Basis for interior cabinet width: Single cabinet with 19 mm side walls

# Accessories for Pro-Line II filing frame.

#### Cross bar for filing maps

Frame depth: 280 / 330 / 385 / 480 mm


Finish: black powder-coated incl. plastic retainers Order data see page 18

#### Wire bracket for filing maps

Track width: 330 mm [A4] Finish: galvanised Order data see page 19

#### Index-card box made of steel

Frame depth: 330 / 480 mm Finish: black powder-coated Order data see chart below




Description	FD	Н	W	WI	Article No.	UQ
Index-card box A4 crosswise	330	210	333,7	323,7	092.09941H	1 pce.
Index-card box A5 crosswise	330	148	222,5	212,5	092.09943H	1 pce.
Index-card box A6 crosswise	330	105	166,9	156,9	092.09945H	1 pce.
Index-card box A4 crosswise	480	210	333,7	323,7	092.09942H	1 pce.
Index-card box A5 crosswise	480	148	222,5	212,5	092.09944H	1 pce.
Index-card box A6 crosswise	480	105	166,9	156,9	092.09946Н	1 pce.
Swivel plate A4 crosswise			333,7	323,7	092.06658H	20 pcs.
Swivel plate A5 crosswise			222,5	212,5	092.06660Н	20 pcs.
Swivel plate A6 crosswise			166,9	156,9	092.06662H	20 pcs.


## Wide drawer conversion.

By assembling a drawer insert, the Pro-Line II filing frame can be converted into an organizable wide drawer. Thanks to its modular construction there are no different parts necessary for filing frames or wide drawers.



#### Assembly:







(1)-(4) like Pro-Line II filing frame (see page 5)


#### (5) Remove the edge profiles

from both front panel and rear panel

#### (6) Install the drawer insert


Fix one border of drawer insert on front panel, then slightly overbend the drawer insert, finally fix other border of drawer insert on rear panel.

Order data for basic equipment see page 18-19 Order data for organisation accessories see page 15-17



# Accessories for Pro-Line II wide drawer.


#### **Drawer partition** for drawer depth 330 mm (A4)





Divider panels and divider plates made of steel, with pastic connection joints Colour: black, UQ: 20 pieces

## Divider panel 330 mm Article No. 092.06669H



#### Partition 3 x A4

#### Demand:

4 divider panels 092.06669H


# 160

## Partition 6 x A5

#### **Demand:**

4 divider panels 092.06669H 3 divider plates 092.08979H






#### Partition 10 x A6

#### **Demand:**

6 divider panels 092.06669H 5 divider plates 092.08528H


# Accessories for Pro-Line II wide drawer.

#### **Drawer partition** for drawer depth 480 mm






Divider panels and divider plates made of steel, with pastic connection joints Colour: black, UQ: 20 pieces



#### Partition $2 \times A4 + 2 \times A5 + 3 \times A6$


#### **Demand:**

- 4 divider panels 092.06692H
- 1 divider plates 092.06688H
- 4 divider plates 092.06689H



# Accessories for Pro-Line II wide drawer.


#### **Index-card formation** for drawer depth 330 mm / 480 mm





made of steel, with pastic connection joints Colour: black, UQ: 20 pieces


Divider panel 330 mm - Article No. 092.06669H Divider panel 480 mm - Article No. 092.06692H



#### Formation 2 x A4 crosswise

#### **Demand:**


3 divider panels 092.06669H/092.06692H i.e. 4 swivel plates 092.06658H



#### Formation 3 x A5 crosswise

#### **Demand:**

4 divider panels 092.06669H/092.06692H i.e. 6 swivel plates 092.06660H




#### Formation 3 x A5 crosswise

#### Demand:

5 divider panels 092.06669H/092.06692H i.e. 8 swivel plates 092.06662H

# Order data - Basic equipment.



No	. Description	Frame depth (mm)*				
		280	330 [A4]	385 [Foolscap]	480	
1	Full extension slide Series 038 premounted assembly with rack, side panel, shroud and 70 mm self-closing device	055.09490H	055.09491H	055.09492H	055.09493H	5 sets
2	Cabinet bracket 4 pieces each filing frame	053.06650	053.06650	053.06650	053.06650	20 pcs.
3	Cross bar (optional) incl. retainers	053.09501H	053.09502H	053.09503H	053.09504H	20 pcs.

 $<sup>^{*}</sup>$  interior cabinet depth depending on cabinet type (see page 8-9)

No.	Description	Frame width (mm) / Interior cabinet width (mm)					
			480 / 562		880 / 962	1080 / 1162	
		[1 x A4]		[2 x A4]		[3 x A4]	
4	Front panel	053.06950H	053.06710H	053.06711H	053.06917H	053.06712H	10 pcs.
5	Rear panel	053.09494H	053.09000H	053.09001H	053.09002H	053.09003H	10 pcs.
6	Connection rod	053.09323H	053.09341H	053.09342H	053.09343H	053.09344H	10 pcs.
	premounted assembly						

]	No.	Description	Frame width (mm) / Interior cabinet width (mm)					UQ
			324 / 406 [1 x A4]	480 / 562	680 / 762 [2 x A4]	880 / 962	1080 / 1162 [3 x A4]	
7	7	Wide drawer insert Drawer depth 330 mm		092.09822H	092.09824H	092.09826H	092.09828H	2 pcs.
	•	Wide drawer insert Drawer depth 480 mm	092.09821H	092.09823H	092.09825H	092.09827H	092.09829H	2 pcs.

## Order data - Accessories.

#### **Installation with front cover:**



#### **Installation behind doors:**



#### Mounting the front cover supports:

The support pieces fix the front cover in upright position.

Filing frame: Insert support pieces from below into the slot of each side panel.

Wide drawer: Remove edge profiles and screw the support pieces from inside in each side panel with self-tapping screw M3 x 6 mm (Article No. 090.09846).

#### Mounting the cover caps:

The cover caps fix the front panel at the side panels of the filing frame.

Put the cover caps (R/L = right/left) on front panel and front end of shroud; pull the edge profile over both cover caps.

No	Description	Finish	Article No.	UQ
7	Wide drawer insert  Dimensions and order data see page 18	black	see page 18	2 pcs.
8	Front cover support	black	092.06651H	20 pairs
9	Cover cap	black	092.06670Н	10 pairs
10	Wire bracket for filing maps	galvanised	092.06673Z	50 pcs.

PLIIHR-1006E Schock 19

# We offer our help.



Give us a call or write to us. Together you and your Schock specialist can work out the optimum solution for you.

